


# Price

On-Site

## PEC Recirculating Filter Loop



### Highlights

- Off line filtration utilizing a low pressure continuous flow is the best way to clean your fluid
- 5 GPM flow rate 110 volt TEFC electric motor
- Choice of filtration including 3 micron absolute with water absorbing
- Pop-up element status indicator
- Bottle sampling valve included upstream of filter
- Can be easily retrofitted to existing systems using our breather adaptor and 2 hoses
- Heat exchanger can also be installed in this loop to cool system fluid
- Recirculation loop can be operated continuously to super clean your systems fluid

*We keep you working.*