

Recirculation Loop



Highlights

- Off line filtration using continuous flow and low pressure is the best way to clean your fluid
- 10 GPM flow rate from quiet vane pump
- Choice of filtration including 3 micron absolute, water absorbing, etc Beta 200
- Differential pop up indicators on both filter heads
- Single and three phase unit available with overload starters
- Built in drip pan along with removable drip pan
- Bottle sampling valve and test point included upstream of filter for particle counting
- Can be easily retrofitted to existing systems using our breather adaptor and 2 hoses
- Heat exchanger can also be installed in this loop to cool system fluid
- Recirculation loop can be operated continuously to super clean your systems fluid

We keep you working.